


Multiple types of fibrous alumina insulation materials were tested to determine their stability in hydrogen gas. Silica bonded types have been known to give superior performance in oxidizing and neutral environments. Alumina bonded types have classically been used as thermal insulation, fixtures and setters in applications where reduction by aggressive furnace atmospheres is encountered. One such aggressive reducing atmosphere is hydrogen, a common cover gas in furnaces for sintering powder metal parts. In hydrogen gas atmospheres, silica - a common binder which imparts high temperature stability and increased mechanical strength - is attacked, dissociates and volatilizes resulting in premature failure of the refractory.



Test Method


Cubes of insulation, roughly 1 inch per side, were measured and weighed. They were fired at 1450°C in a model 1725 HTF box furnace manufactured by CM Furnaces, Inc. The furnace was purged with 15 scfh hydrogen gas with a dew point of <40°C. It was heated at a rate of 200°C / hour with soak times of 1, 2, 10 and 50 hours. The samples were removed after each soak, measured and weighed. Weight loss and thickness shrinkage were calculated using experimental data. Shrinkage in the length and width directions were averaged to obtain the data displayed. The materials tested are described in the following table.

Type	Density	Bond	Comment
SALI	30 pcf	Silica	Premium grade mid density material
AL 25/1700	25 pcf	Silica	Economy grade mid density material with filler
ZAL-15AA	15 pcf	Alumina	Premium grade low density material
ECO-20AA	20 pcf	Alumina	Economy grade mid density material with filler
ZAL-45AA	45 pcf	Alumina	Premium grade high density material
ZAL-60AA	60 pcf	Alumina	Specially prepared high density material

Results


Weight Loss results for all types tested.

WEIGHT LOSS vs TIME at 1450°C in HYDROGEN




Weight Loss results for alumina bonded types tested.

WEIGHT LOSS vs TIME at 1450°C in HYDROGEN




Shrinkage results in length and width directions for all types tested.

**LENGTH and WIDTH SHRINKAGE vs TIME
at 1450°C in HYDROGEN**



Shrinkage results in thickness directions for all types tested.

**THICKNESS SHRINKAGE vs TIME
at 1450°C in HYDROGEN**



Conclusions

Premium (ZAL-45AA) and special (ZAL-60AA) grade fibrous alumina insulation materials appear best suited for use as thermal insulation, fixtures and setters in furnaces with hydrogen atmospheres as they exhibited the least weight loss and thermal shrinkage of all specimens tested.

Alumina bonded materials (ZAL-15AA, ECO-20AA, ZAL-45AA and ZAL-60AA) showed significantly less weight loss after exposure to hydrogen gas at 1450°C than did the silica bonded types tested.

Silica bonded materials (SALI and AL 25/1700) exhibited significant weight loss after testing at 1450°C in hydrogen.

Thermal shrinkage is inversely proportional to density, independent of the bond type.

Acknowledgement

The data presented in this article was collected by CM Furnaces, Inc (www.cmfurnaces.com) and provided to ZIRCAR Ceramics, Inc. by their Director of Research and Development, Donald T. Whychell Sr. (dwhyhell@cmfurnaces.com)